

# MA882/MA883/MA884/MA885

## Digital Refractometers for Grape Juice Must Measurements

The MA882, MA883, MA884 and MA885 are optical instruments that are based on the measurement of the refractive index of a solution. The measurement of refractive index is simple and quick and provides the vintner an accepted method for sugar content analysis. Samples are measured after a simple user calibration with deionized or distilled water. Within seconds the instrument measures the refractive index of the grape. This digital refractometers eliminate the uncertainty associated with mechanical refractometers and are easily portable for measurements in the field. The four instruments utilize internationally recognized references for unit conversion and temperature compensation.

- MA882 measures %Brix;
- MA883 measures °Baumé;
- MA884 measures %Brix and Potential Alcohol (% vol);
- MA885 measures %Brix, °Oechsle (°Oe) and °KMW (°Babo).

Temperature (in °C or °F) is displayed simultaneously with the measurement on the large dual level display along with icons for Low Power and other helpful message codes.

### Key features include:

- Dual-level LCD
- Automatic Temperature Compensation (ATC)
- Easy setup and storage
- Battery operation with Low Power indicator (BEPS)
- Automatically turns off after 3 minutes of non-use



- Years warranty 2
- ATC
- Dual Display
- Self diagnostics
- CE

Specifications	MA882	MA883	MA884	MA885
Range	0 to 50% Brix 0 to 80°C / 32 to 176°F	0 to 28 °Baumé 0 to 80°C / 32 to 176°F	0 to 50% Brix 0 to 25% v/v Potential Alcohol 0 to 80°C / 32 to 176°F	0 to 50% Brix 0 to 230°Oechsle 0 to 42 °KMW 0 to 80°C / 32 a 176°F
Resolution	0.1% Brix 0.1°C / 0.1 °F	0.1 °Baumé 0.1°C / 0.1 °F	0.1% Brix 0.1% v/v Potential Alcohol 0.1°C / 0.1°F	0.1% Brix 0.1 °Oechsle 0.1 °KMW 0.1°C / 0.1°F
Accuracy	±0.2% Brix ±0.3°C / ±0.5°F	±0.1 °Baumé ±0.3°C / ±0.5°F	±0.2% Brix ±0.2 v/v Potential Alcohol ±0.3°C / ±0.5°F	±0.2% Brix ±1°Oechsle ±0.2 °KMW ±0.3°C / ±0.5°F
Light Source	yellow LED	yellow LED	yellow LED	yellow LED
Measurement Time	approximately 1.5 seconds	approximately 1.5 seconds	approximately 1.5 seconds	approximately 1.5 seconds
Minimum Sample Volume	100 µL (cover prism totally)	100 µL (cover prism totally)	100 µL (cover prism totally)	100 µL (cover prism totally)
Sample Cell	SS ring and flint glass prism	SS ring and flint glass prism	SS ring and flint glass prism	SS ring and flint glass prism
Temperature Compensation	automatic between 10 and 40°C / 50 to 104°F	automatic between 10 and 40°C / 50 to 104°F	automatic between 10 and 40°C / 50 to 104°F	automatic between 10 and 40°C / 50 to 104°F
Case Material	ABS	ABS	ABS	ABS
Enclosure Rating	IP 65	IP 65	IP 65	IP 65
Battery Type	1 x 9V AA (included)	1 x 9V AA (included)	1 x 9V AA (included)	1 x 9V AA (included)
Battery Life	5000 reading	5000 reading	5000 reading	5000 reading
Auto-shut off	after 3 minutes of non-use	after 3 minutes of non-use	after 3 minutes of non-use	after 3 minutes of non-use
Dimensions	192 x 102 x 67 mm	192 x 102 x 67 mm	192 x 102 x 67 mm	192 x 102 x 67 mm
Weight	420 g	420 g	420 g	420 g

### Ordering Information

MA882, MA883, MA884 and MA885 are supplied complete with Mi0005 9V battery and instruction manual.



Click to buy: [www.eseasongear.com](http://www.eseasongear.com)